

Variphone Soft




CUSTOM MADE HEARING PROTECTION

Variphone Soft is a new generation of hearing protection. Variphone otoplastics are the most advanced hearing protectors on the market. The Variphone Soft is unique because it is the first and only fully custom made silicone hearing protection product that has a 2-canal filter module. This filter module makes no-fuss testing of the hearing protector possible (leaktight test). The hearing protector has modular components and thanks to the click-in unit with adjustable filter, attenuation can be very finely tuned.

In practice this means that communication is maintained and emergency warnings can still be heard. The hearing protector perfectly dovetails with the HearingCoach hearing care programme with this 2-canal filter module too.

This hearing protector is suitable for workers who want a revolutionary, durable and high-quality hearing protector that is manufactured from a soft material. It is specifically measured for each individual and therefore guarantees a perfect fit and maximum wearing comfort.

The grip allows easy insertion in and removal of the hearing protector from the ear canal. The Variphone Soft is therefore an ideal combination of maximum wearing comfort and optimum protection against noise. This grip also makes provision for a cord to be attached to it.




Variphone soft

Process flow

A set of ear impressions are required, which are sent to our laboratories for the manufacturing of the hearing protectors. One of our experts will visit you on site for an ear inspection and making of the ear impressions. The ear impressions are sent to us and manufacturing in the laboratory can commence. A second visit by one of our specialists is necessary. During this second visit the Variphone Soft hearing protector will be fitted and tested for proper functioning (leaktight test) and the amount of attenuation will be set. This check is performed using a digital measuring device called a SEAL tester. During this consultation the user will receive instructions on wearing and maintaining the hearing protectors.

Accessories

Variphone Soft hearing protectors are supplied with a storage pouch and an instruction manual, cleaning cloth and earwax remover as standard.



1. Silicone earpiece
2. Adjusting pin
3. Ventilation canal
4. Testing canal
5. Cap
6. Filter module
7. Mouth of valve
8. Filter module
9. Mouth of leaktight testing canal

Options



Various colours
Cord
Ball bearing

Specifications

Classification: unique 2-canal design with adjustable attenuation
Material: 70 shore silicone material
Special parts: adjustable valve with second leak test canal, red and blue caps (L-R coding)

Approval

DIN EN352-2: 2003



■ AUTHORISED DEALER